




DILUTION UNIT ON MOUNTING PLATE

On opening the tap, the dilution unit automatically dispenses a volume of SeptiOne Pro cleaning product at the optimum dilution (dilution 0.5%).



The base plate has 4 holes for fixing the unit to the wall.

ABYSSNAUT® – 3, rue de l'Orme - 63 880 OLLIERGUES – France. Tel./Fax: +33 (0)4 73 95 29

68

www.abyssnaut.com - contact@abyssnaut.com



PRACTICAL ADVANTAGES:

- *No need to calculate the volume of cleaning product in relation to water volume*
- *Cleaning product automatically mixed with the water volume, providing a uniform disinfectant product*
- *No need to connect to any power outlet*
- *Simple installation*

METHOD OF INSTALLATION:

- *Fix the unit to a vertical surface*
- *Attach a flexible hose (such as a garden hose) with diameter 15mm to the quick-fit connector (of the type GARDENA) supplied and connect the hose to a water intake (minimum pressure: 1.2 bars).*
- *Place the strainer in the ABYSSNAUT can, screw the attached cap to the hose (small hose).*
- *If necessary, you can shorten the mixed product dispensing pipe (large diameter pipe).*

USE INSTRUCTIONS:

- *Once all the connections have been made:*
- *Open the sector's water intake*
- *Press the blue button to dispense the product.*
- *Turn the button a 1/4 turn to trigger continuous dispensing.*
- *Repeat this operation in reverse to stop dispensing the product.*
-

STAY CLOSE TO THE TANK TO AVOID ANY OVERFLOW.

Dimensions of the complete system (plate + unit):

- Height: 300 mm
 - Width: 180 mm
 - Thickness: 120 mm
-

KEEP OUT OF REACH OF CHILDREN

Made in FRANCE

ABYSSNAUT® – 3, rue de l'Orme - 63 880 OLLIERGUES – France. Tel./Fax: +33 (0)4 73 95 29

68

www.abyssnaut.com - contact@abyssnaut.com